

**Standby Power Rating**  
 200 kW, 250 kVA, 60 Hz



\*Assembled in the USA using domestic and foreign parts.

\*EPA Certified Prime ratings are not available in the US or its Territories.




Image used for illustration purposes only

## Codes and Standards

**Not all codes and standards apply to all configurations. Contact factory for details.**



UL2200, UL6200, UL1236, UL489, UL142



CSA C22.2, ULC S601



BS5514 and DIN 6271



SAE J1349



NFPA 37, 70, 99, 110



NEC700, 701, 702, 708



NEMA ICS10, MG1, 250, ICS6, AB1



ANSI C62.41



IBC 2021, IBC 2024, IBC 2027, CBC 2022, CBC 2025, CBC 2028, ASCE 7-16, ASCE 7-22

## Powering Ahead

For over 60 years, Generac has provided innovative design and superior manufacturing.

Generac provides superior quality by designing and manufacturing most of its generator components, including alternators, enclosures and base tanks, control systems and communications software.

Generac gensets utilize a wide variety of options, configurations and arrangements, allowing us to meet the standby power needs of practically every application.

Generac searched globally for the most reliable engines to power our generators. We choose only engines that have already been proven in heavy-duty industrial applications under adverse conditions.

Generac is committed to ensuring our customers' service support continues after their generator purchase.

## STANDARD FEATURES

### ENGINE SYSTEM

- Oil Drain Extension
- Heavy Duty Air Cleaner
- Level 1 Fan and Belt Guards
- Stainless Steel Flexible Exhaust Connection
- Factory Filled Oil and Coolant
- Radiator Duct Adapter (Open Set Only)
- Block Heater

### FUEL SYSTEM

- Fuel Lockoff Solenoid
- Primary Fuel Filter

### COOLING SYSTEM

- Closed Coolant Recovery System
- UV/Ozone Resistant Hoses
- Factory-Installed Radiator
- Radiator Drain Extension
- 50/50 Ethylene Glycol Antifreeze

### ELECTRICAL SYSTEM

- Battery Charging Alternator
- Battery Cables
- Battery Tray
- Rubber-Booted Engine Electrical Connections
- Solenoid Activated Starter Motor

### ALTERNATOR SYSTEM

- GENprotect™
- 12 Leads (3-Phase, Non 600V)
- Class H Insulation Material
- Vented Rotor
- 2/3 Pitch
- Skewed Stator
- Auxiliary Voltage Regulator Power Winding
- Permanent Magnet Excitation
- Sealed Bearings
- Automated Manufacturing (Winding, Insertion, Lacing, Varnishing)
- Rotor Dynamically Spin Balanced
- Amortisseur Winding
- Full Load Capacity Alternator
- Protective Thermal Switch

### GENERATOR SET

- Generac Link Connectivity Hardware
- Internal Genset Vibration Isolation
- Separation of Circuits - High/Low Voltage
- Separation of Circuits - Multiple Breakers
- Wrapped Exhaust Piping
- Standard Factory Testing
- 2 Year Extended Limited Warranty (Standby Rated Units)
- 1 Year Extended Limited Warranty (Prime Rated Units)

### ENCLOSURE (IF SELECTED)

- Silencer Mounted in the Discharge Hood
- Rust-Proof Fasteners with Nylon Washers to Protect Finish
- High Performance Sound-Absorbing Material (Sound Attenuated Enclosures)
- Gasketed Doors
- Upward Facing Discharge Hoods (Radiator and Exhaust)
- Stainless Steel Lift Off Door Hinges
- Stainless Steel Lockable Handles
- RhinoCoat™ - Textured Polyester Powder Coat Paint

### TANKS (IF SELECTED)

- UL 142/ULC S601
- Double Wall
- Vents
- Sloped Top
- Sloped Bottom
- Factory Pressure Tested - 2 psi
- Rupture Basin Alarm
- Fuel Level
- Check Valve In Supply and Return Lines
- RhinoCoat™ - Textured Polyester Powder Coat Paint

## CONTROL SYSTEM



### DSE G8601 Controller

#### Key Features

- Advanced PLC Functionality
- Multi-Purpose PIDs
- Virtual Inputs
- On-Screen Mimic (SLDs)
- Multiple Application Support
- Multi-Level Pin Protected Front Panel Editor
- Integral LCD Display Heater
- Enhanced High-Resolution 240 x 128 Pixel Display
- Single Generator Control
- Latest ECU/ECM Support
- Touch Screen Panel PC Support
- Zero Sequence Voltage Protection
- Integral Gasket (IP65 protection)

#### Standard Protections

- Low Coolant Level
- High/Low Coolant Temperature
- Oil Temperature
- Over/Under Speed
- Over/Under Voltage
- Over/Under Frequency

- Over/Under Current
- Over Load
- Battery Voltage
- Battery Charger Current
- Phase to Phase and Phase to Neutral Short Circuits (I<sup>2</sup>T Algorithm)
- Ground Fault

#### Control Panel

- Auto/Off/Manual
- Indication Through Display Screen
- Audible Alarm and Silence
- Not in Auto Indication

#### Voltage Regulation

- Digital Control
- Three-Phase Sensing
- Negative Power Limit
- Loss of Sensing Protection
- Fault Protection (I<sup>2</sup>T Function)
- High Voltage Limit
- Low Voltage Limit
- Maximum Power Limit
- $\pm 0.5\%$  Voltage Regulation

#### Governor Functionality

- Speed Control through ECM Integration
- Soft Start Ramping (Multiple Steps)

#### Qualification Testing

- Life Test in Environmental Chamber
- Temperature Rating -22 °F to +122 °F (-30 °C to +50 °C)
- Vibration Tested and Protected

#### Connections (Actual I/O May Vary Due to Configuration)

- 4 Analog Inputs
- 12 Digital Inputs
  - 9 Active Low Digital Outputs

#### Customer Ports

- Ethernet
- 2 RS-485
- 2 USB
- CANBus

#### Codes and Standards

- UL 6200
- CE
- NFPA 110 Capable

#### More Features

- Built-in Governor
- Digital AVR Support
- Multiple Language Support
- Three-Phase Generator Sensing and Protection
- Three-Phase Bus Sensing
- Generator Current, Protection and Power Monitoring
- Configurable Timers
- Integrated SNMP
- Data Logging
- PC Configuration
- DSENet<sup>®</sup> (Expansion Support)
- Flexible I/O (Inputs/Outputs)
- Automatic and Front Panel Breaker Control
- Power-Save Mode

## CONFIGURABLE OPTIONS

### ENGINE SYSTEM

- Air Filter Restriction Indicator
- Oil Heater
- Exhaust Silencer - Shipped Loose (Open Set Only)

### FUEL SYSTEM

- NPT Flexible Fuel Line

### ELECTRICAL SYSTEM

- 10A UL Battery Charger
- Battery Warmer

### ALTERNATOR SYSTEM

- Alternator Upsizing
- Anti-Condensation Heater
- Tropical Coating

### CIRCUIT BREAKER OPTIONS

- Main Line Circuit Breaker
- 2<sup>nd</sup> Main Line Circuit Breaker
- Shunt Trip and Auxiliary Contact
- Electronic Trip Breakers

### GENERATOR SET

- Extended Factory Testing
- IBC Seismic Certification
- HCAI/OSHPD Seismic Certification
- 12 Position Load Center
- Spring Vibration Isolators
- Radiator Stone Guard (Open Set Only)
- Critical Silencer Flange - Shipped Loose (Open Set Only)

### ENCLOSURE

- Weather Protected Enclosure
- Level 1 Sound Attenuated
- Level 2 Sound Attenuated
- Level 2 Sound Attenuated with Motorized Dampers
- Steel Enclosure
- Aluminum Enclosure
- Up to 200 MPH Wind Load Rating (Contact Factory for Availability)
- AC/DC Enclosure Lighting Kit
- Door Alarm Switch
- Enclosure Heater (with Motorized Dampers Only)

### FUEL TANKS (SIZES ON LAST PAGE)

- 8 in (203.2 mm) Fill Extension
- 13 in (330.2 mm) Fill Extension
- Overfill Protection Valve
- 5 Gal Spill Return Hose
- Tank Risers
- Florida DEP-DERM
- Vent Extensions
- Fire Rated Fuel Hose

### CONTROL SYSTEM

- NFPA 110 Compliant 21-Light Remote Annunciator
- Remote Relay Assembly (8 or 16)
- Remote E-Stop (Break Glass-Type, Surface Mount)
- Remote E-Stop (Red Mushroom-Type, Surface Mount)
- Remote E-Stop (Red Mushroom-Type, Flush Mount)
- 10A Engine Run Relay
- Ground Fault Annunciator
- 100 dB Alarm Horn
- 120 V GFCI Outlet
- Flush Mount Annunciator Kit
- Remote Communication - Modem
- Damper Alarm Contacts (with Motorized Dampers Only)

### WARRANTY (STANDBY GENSETS ONLY)

- 2 Year Extended Limited Warranty
- 5 Year Extended Limited Warranty
- 7 Year Extended Limited Warranty
- 10 Year Extended Limited Warranty

EPA Certified Stationary Emergency

**APPLICATION AND ENGINEERING DATA**

**ENGINE SPECIFICATIONS**

General

Make	Iveco/FPT
EPA Emissions Compliance	Stationary Emergency
EPA Emissions Reference	See Emission Data Sheet
Cylinder #	6
Type	In-line
Displacement - L (in <sup>3</sup> )	530.91 (8.7)
Bore - mm (in)	4.61 (117)
Stroke - mm (in)	5.31 (135)
Compression Ratio	16.5:1
Intake Air Method	Turbocharged/Aftercooled
Cylinder Head	4 Valve
Piston Type	Aluminum
Crankshaft Type	Forged Steel

Engine Governing

Governor	Electronic Isochronous
Frequency Regulation (Steady State)	±0.25%

Lubrication System

Oil Pump Type	Gear
Oil Filter Type	Full-Flow Cartridge
Crankcase Oil Capacity - L(qts)	28.0 (29.6)

Cooling System

Cooling System Type	Closed Recovery
Water Pump Type	Pre-Lubed, Self Sealing
Fan Type	Pusher
Fan Speed - RPM	2,538
Fan Diameter - mm (in)	30 (762)

Fuel System

Fuel Type	Ultra Low Sulfur Diesel Fuel #2
Fuel Specifications	ASTM
Fuel Filtering (Microns)	5
Fuel Inject Pump Make	Electronic
Fuel Pump Type	Engine Driven Gear
Injector Type	Common Rail
Engine Type	Direct Injection
Fuel Supply Line - mm (in)	0.5 (12.7) NPT
Fuel Return Line - mm (in)	0.5 (12.7) NPT

Engine Electrical System

System Voltage	24 VDC
Battery Charger Alternator	Standard
Battery Size	See Battery Index 0161970SBY
Battery Voltage	(2)-12 VDC
Ground Polarity	Negative

**ALTERNATOR SPECIFICATIONS**

Standard Model	K0250124Y21
Poles	4
Field Type	Revolving
Insulation Class - Rotor	H
Insulation Class - Stator	H
Total Harmonic Distortion	<5%
Telephone Interference Factor (TIF)	<50

Standard Excitation	Permanent Magnet Excitation
Bearings	Single Sealed Cartridge
Coupling	Direct via Flexible Disc
Prototype Short Circuit Test	Yes
Voltage Regulator Type	Digital
Number of Sensed Phases	All
Regulation Accuracy (Steady State)	±0.25%

EPA Certified Stationary Emergency

**OPERATING DATA**

**POWER RATINGS - DIESEL**

Standby		
Single-Phase 120/240 VAC @1.0pf	200 kVA/200 kW	Amps: 833
Three-Phase 120/208 VAC @0.8pf	250 kVA/200 kW	Amps: 694
Three-Phase 120/240 VAC @0.8pf	250 kVA/200 kW	Amps: 601
Three-Phase 277/480 VAC @0.8pf	250 kVA/200 kW	Amps: 301
Three-Phase 346/600 VAC @0.8pf	250 kVA/200 kW	Amps: 241

**MOTOR STARTING CAPABILITIES (SKVA)**

skVA vs. Voltage Dip			
277/480 VAC 3Ø	30%	208/240 VAC 3Ø	30%
K0200124Y21	478	K0200124Y21	361
K0250124Y21	630	K0250124Y21	506
K0300124Y21	790	K0300124Y21	609
K0350124Y21	1001	K0350124Y21	801

**FUEL CONSUMPTION RATES\***

Fuel Pump Lift - ft (m)	Diesel - gph (Lph)	
	Percent Load	Standby
3 (1)	25%	5.1 (19.3)
Total Fuel Pump Flow (Combustion + Return) - gph (Lph)	50%	9.6 (36.3)
	75%	13.7 (51.9)
	100%	17.0 (64.3)
	*Fuel supply installation must accommodate fuel consumption rates at 100% load.	

**COOLING**

Standby		
Coolant Flow	gpm (Lpm)	63.3 (240)
Coolant System Capacity	gal (L)	12.7 (49.2)
Heat Rejection to Coolant	BTU/hr (kW)	545,646 (160)
Inlet Air	cfm (m <sup>3</sup> /hr)	8,872 (251)
Maximum Operating Ambient Temperature	°F (°C)	110 (43.3)
Maximum Operating Ambient Temperature (Before Derate)	See Bulletin No. 0199280SSD	
Maximum Additional Radiator Backpressure	in H <sub>2</sub> O (kPa)	0.5 (0.12)

**COMBUSTION AIR REQUIREMENTS**

Standby	
Flow at Rated Power - cfm (m <sup>3</sup> /min)	595 (16.8)

**ENGINE**

Standby		
Rated Engine Speed	RPM	1,800
Horsepower at Rated kW**	hp	320
Piston Speed	ft/min (m/min)	1,593 (486)
BMEP	psi (kPa)	265 (1,827)

\*\*Refer to "Emissions Data Sheet" for maximum 305 (2,103) m BHP for EPA and SCAQMD permitting purposes.

**EXHAUST**

Standby		
Exhaust Flow (Rated Output)	cfm (m <sup>3</sup> /min)	1345 (38.1)
Maximum Allowable Backpressure	inHg (kPa)	1.5 (5.1)
Exhaust Temperature (Rated Output)	°F (°C)	920 (493)

Deration – Operational characteristics consider maximum ambient conditions. Derate factors may apply under atypical site conditions.

Please contact a Generac Power Systems Industrial Dealer for additional details. All performance ratings in accordance with BS5514 and DIN6271 standards.

Standby - See Bulletin 0187500SSB



Prime - See Bulletin 0187510SSB

# SD200 | 8.7L | 200 kW

## INDUSTRIAL DIESEL GENERATOR SET



EPA Certified Stationary Emergency

### DIMENSIONS AND WEIGHTS\*



#### OPEN SET

Run Time - Hours	Usable Capacity - gal (L)	L x W x H - in (mm)	Weight - lbs (kg)**	
			Steel	Aluminum
No Tank	-	128.0 (3,251) x 53.4 (1,357) x 58.0 (1,473)	5,108 (2,317)	
9	153 (579)	128.0 (3,251) x 53.4 (1,357) x 71.0 (1,803)	6,113 (2,773)	
21	372 (1,408)	128.0 (3,251) x 53.4 (1,357) x 83.0 (2,108)	6,535 (2,964)	
34	589 (2,229)	128.0 (3,251) x 53.4 (1,357) x 95.0 (2,143)	6,952 (3,153)	
40	693 (2,623)	136.0 (3,454) x 53.4 (1,357) x 95.0 (2,143)	6,673 (3,027)	
55	946 (3,581)	208.3 (5,292) x 53.4 (1,357) x 99.0 (2,515)	8,133 (3,689)	
77	1,325 (5,016)	277.8 (7,055) x 53.4 (1,357) x 97.4 (2,473)	9,148 (4,150)	



#### LEVEL 0 SOUND ATTENUATED ENCLOSURE



Run Time - Hours	Usable Capacity - Gal (L)	L x W x H - in (mm)	Weight - lbs (kg)**	
			Steel	Aluminum
No Tank	-	154.4 (3,923) x 54.0 (1,371) x 69.8 (1,772)	6049 (2744)	5582 (2532)
9	153 (579)	154.4 (3,923) x 54.0 (1,371) x 82.8 (2,102)	7054 (3200)	6587 (2988)
21	372 (1,408)	154.4 (3,923) x 54.0 (1,371) x 94.8 (2,407)	7476 (3391)	7009 (3179)
34	589 (2,229)	154.5 (3,923) x 54.0 (1,371) x 106.8 (2,712)	7893 (3580)	7426 (3368)
40	693 (2,623)	154.5 (3,923) x 54.0 (1,371) x 106.8 (2,712)	7614 (3454)	7147 (3242)
55	946 (3,581)	208.3 (5,292) x 54.0 (1,371) x 110.8 (2,814)	9074 (4116)	8607 (3904)
77	1,325 (5,016)	277.8 (7,055) x 54.0 (1,371) x 109.1 (2,772)	10089 (4576)	9622 (4364)

\* All measurements are approximate and for estimation purposes only. Specification characteristics may change without notice. Please contact a Generac Power Systems Industrial Dealer for detailed installation drawings. Extended and not extended tank offerings vary. Contact dealer for options.

\*\* Weights shown represent maximum configurations with heaviest available options installed.



EPA Certified Stationary Emergency

**DIMENSIONS AND WEIGHTS\***





**LEVEL 1 SOUND ATTENUATED ENCLOSURE**

Run Time - Hours	Usable Capacity - Gal (L)	L x W x H - in (mm)	Weight - lbs (kg)**	
			Steel	Aluminum
No Tank	-	179.9 (4,569) x 54.0 (1,371) x 68.7 (1,745)	6354 (2882)	5714 (2592)
9	153 (579)	179.9 (4,569) x 54.0 (1,371) x 81.7 (2,075)	7359 (3338)	6719 (3048)
21	372 (1,408)	179.9 (4,569) x 54.0 (1,371) x 93.7 (2,380)	7781 (3529)	7141 (3239)
34	589 (2,229)	179.9 (4,569) x 54.0 (1,371) x 105.7 (2,685)	8198 (3716)	7558 (3428)
40	693 (2,623)	179.9 (4,569) x 54.0 (1,371) x 105.7 (2,685)	7919 (3592)	7279 (3302)
55	946 (3,581)	208.3 (5,292) x 54.0 (1,371) x 109.7 (2,786)	9379 (4254)	8739 (3964)
77	1,325 (5,016)	277.8 (7,055) x 54.0 (1,371) x 108.1 (2,745)	10394 (4715)	9754 (4424)



**LEVEL 2 SOUND ATTENUATED ENCLOSURE**

Run Time - Hours	Usable Capacity - Gal (L)	L x W x H - in (mm)	Weight - lbs (kg)**	
			Steel	Aluminum
No Tank	-	154.5 (3,924) x 54.0 (1,371) x 99.4 (2,525)	6590 (2989)	5816 (2638)
9	153 (579)	154.5 (3,924) x 54.0 (1,371) x 112.4 (2,856)	7595 (3445)	6821 (3094)
21	372 (1,408)	154.5 (3,924) x 54.0 (1,371) x 124.4 (3,160)	8017 (3636)	7243 (3285)
34	589 (2,229)	154.5 (3,924) x 54.0 (1,371) x 136.4 (3,465)	8434 (3826)	7660 (3475)
40	693 (2,623)	154.5 (3,924) x 54.0 (1,371) x 136.4 (3,465)	8155 (3699)	7381 (3348)
55	946 (3,581)	208.3 (5,292) x 54.0 (1,371) x 140.4 (3,567)	9615 (4361)	8841 (4010)
77	1,325 (5,016)	277.8 (7,055) x 54.0 (1,371) x 138.8 (3,525)	10630 (4822)	9856 (4471)



**LEVEL 2 SOUND ATTENUATED ENCLOSURE WITH DAMPERS**

Run Time - Hours	Usable Capacity - Gal (L)	L x W x H - in (mm)	Weight - lbs (kg)**	
			Steel	Aluminum
No Tank	-	154.5 (3,696) x 54 (1,372) x 100.5 (2,553)	6775 (3073)	6001 (2722)
9	153 (579)	154.5 (3,696) x 54 (1,372) x 113.5 (2,883)	7780 (3529)	7006 (3179)
21	372 (1,408)	154.5 (3,696) x 54 (1,372) x 125.5 (3,188)	8202 (3720)	7428 (3369)
34	589 (2,229)	154.5 (3,696) x 54 (1,372) x 137.5 (3,493)	8619 (3910)	7845 (3558)
10	693 (2,623)	154.5 (3,696) x 54 (1,372) x 137.5 (3,493)	8340 (3783)	7566 (3432)
55	946 (3,581)	208.3 (5,291) x 54 (1,372) x 141.5 (3,594)	9800 (4445)	9026 (4094)
77	1,325 (5,016)	277.8 (7,056) x 54 (1,372) x 140 (3,556)	10815 (4906)	10041 (4555)

\* All measurements are approximate and for estimation purposes only. Specification characteristics may change without notice. Please contact a Generac Power Systems Industrial Dealer for detailed installation drawings. Extended and not extended tank offerings vary. Contact dealer for options.

\*\* Weights shown represent maximum configurations with heaviest available options installed.